

Flat Traveling Cable Type ETP/300V

UNSUPPORTED - UL LISTED, CSA CERTIFIED, NEC/CEC COMPLIANT

Power and signal conductors



Part Number	Product Code	Number/Size of Conductors	Max. Hang Length feet • meters	Cable Nom. Dim H x W inches • mm	Cable Net Weight lbs/kft • kg/km
18-008-07	P 8-18	8 / 18 AWG	150 • 46	.19 x 1.00 • 4.8 x 25.4	145 • 215
18-009-07	P 9-18	9 / 18 AWG	150 • 46	.19 x 1.01 • 4.8 x 25.6	137 • 203
18-010-07	P 10-18	10 / 18 AWG	150 • 46	.19 x 1.07 • 4.8 x 27.2	157 • 233
18-012-07	P 12-18	12 / 18 AWG	150 • 46	.19 x 1.30 • 4.8 x 33.0	210 • 312
18-016-07	P 16-18	16 / 18 AWG	150 • 46	.19 x 1.67 • 4.8 x 42.4	235 • 349
18-020-07	P 20-18	20 / 18 AWG	150 • 46	.19 x 2.30 • 4.8 x 58.4	296 • 440
18-024-07	P 24-18	24 / 18 AWG	150 • 46	.19 x 2.70 • 4.8 x 68.6	367 • 546
18-208-07	P 8-16	8 / 16 AWG	150 • 46	.20 x 0.97 • 5.1 x 24.6	156 • 232
18-212-07	P 12-16	12 / 16 AWG	150 • 46	.20 x 1.50 • 5.1 x 38.1	231 • 343
18-224-07	P 24-16	16 / 16 AWG	150 • 46	.20 x 2.90 • 5.1 x 73.7	462 • 686
18-412-07	P 12-14	12 / 14 AWG	150 • 46	.26 x 2.00 • 6.6 x 50.8	366 • 543



Shielded pairs



Part Number	Product Code	Number/Size of Conductors	Max. Hang Length feet • meters	Cable Nom. Dim H x W inches • mm	Cable Net Weight lbs/kft • kg/km
18-X04-07	P 4X20SH	4 shielded pair / 20 AWG	150 • 46	.30 x .940 • 7.62 x 23.9	184 • 273
18-X08-07	P 8X20SH	8 shielded pair / 20 AWG	150 • 46	.30 x 2.00 • 7.62 x 50.8	430 • 638



Unitized conductors / power and signal conductors



Part Number	Product Code	Number/Size* of Conductors	Max. Hang Length feet • meters	Cable Nom. Dim H x W inches • mm	Cable Net Weight lbs/kft • kg/km
18-040-07	G 40-18 UNITIZED	40 / 18 AWG	150 • 46	.39 x 1.90 • 9.9 x 48.3	524 • 778
18-C28-07	GCX 31	28 / 18 AWG 3 RG6/U coax	150 • 46	.375 x 2.20 • 9.5 x 55.9	565 • 839



Use these tools to prepare Super-Flex traveling cable. See pages 90 - 91 for details.

FCJ flat cable stripper



QuickStrip wire stripper



Automatic wire stripper



Manual wire stripper



Flat Traveling Cable Type ETP/300V

UNSUPPORTED - UL LISTED, CSA CERTIFIED, NEC/CEC COMPLIANT

Power and signal conductors



Part Number	Product Code	Number/Size of Conductors	Max. Hang Length feet • meters	Cable Nom. Dim H x W inches • mm	Cable Net Weight lbs/kft • kg/km
18-X11-07	PC11	3 / 14 AWG 4 shielded pair / 20 AWG	150 • 46	.29 x 1.55 • 7.4 x 39.4	345 • 512
18-216-07	PC16	2 / 14 AWG 1 shielded pair / 14 AWG 6 shielded pair / 18 AWG	150 • 46	.43 x 2.40 • 10.9 x 61.0	690 • 1024
18-410-07	PC16	4 / 14 AWG 10 / 18 AWG 1 shielded pair / 20 AWG	150 • 46	.29 x 2.20 • 7.4 x 55.9	490 • 728
18-A16-07	PC16A	4 / 14 AWG 10 / 18 AWG 1 shielded pair / 20 AWG	150 • 46	.29 x 2.20 • 7.4 x 55.9	490 • 728
18-C16-07	PC16	4 / 14 AWG 12 / 18 AWG	150 • 46	.23 x 1.91 • 5.8 x 48.5	385 • 572
18-C17-07	PCX17	8 shielded pair / 20 AWG 1 coax / RG6/U	150 • 46	.44 x 2.2 • 11.2 x 55.9	497 • 740
18-618-07	PC 18 SP [†]	6 / 14 AWG 12 / 18 AWG	150 • 46	.23 x 2.19 • 5.8 x 55.6	401 • 597
18-C18-07	PC 18	6 / 14 AWG 12 / 18 AWG	150 • 46	.23 x 2.19 • 5.8 x 55.6	401 • 597
18-218-07	PC 18	2 / 14 AWG 12 / 18 AWG 2 twisted pair / 20 AWG	150 • 46	.23 x 1.20 • 5.8 x 30.5	330 • 490
18-318-07	PC 18 LO	2 / 14 AWG 12 / 18 AWG (conductors 1 - 10 are yellow; 11 - 12 are orange) 2 shielded pair / 20 AWG	150 • 46	.29 x 2.0 • 7.4 x 50.8	424 • 631
18-418-07	PC 18 HI	2 / 14 AWG 12 / 18 AWG (conductors 13 - 20 are orange; 21 - 24 are tan) 2 shielded pair / 20 AWG	150 • 46	.29 x 2.0 • 7.4 x 50.8	424 • 631

[†]“SP” denotes special color coding and/or conductor numbering



Flat Traveling Cable Type ETP/300V

UNSUPPORTED - UL LISTED, CSA CERTIFIED, NEC/CEC COMPLIANT



Power and signal conductors

Part Number	Product Code	Number/Size of Conductors	Max. Hang Length feet • meters	Cable Nom. Dim H x W inches • mm	Cable Net Weight lbs/kft • kg/km
18-021-07	PC21	3 / 14 AWG 14 / 18 AWG 2 shielded pair / 20 AWG	150 • 46	.29 x 2.35 • 7.4 x 59.7	499 • 741
18-C21-07	PCX21	4 / 14 AWG 10 / 18 AWG 3 shielded pair / 20 AWG 1 RG6/U coax	150 • 46	.375 x 2.80 • 9.5 x 71.1	715 • 1062
18-421-07	PC21 SP †	5 / 16 AWG 8 / 18 AWG 4 twisted pair / 20 AWG	150 • 46	.29 x 2.33 • 7.4 x 59.2	494 • 733
18-X22-07	PC22	4 / 14 AWG 10 / 18 AWG 4 shielded pair / 20 AWG	150 • 46	.29 x 2.65 • 7.4 x 67.3	639 • 935
18-025-07	PC25	3 / 14 AWG 18 / 18 AWG 2 shielded pair / 20 AWG	150 • 46	.29 x 2.75 • 7.4 x 69.9	593 • 880
18-C26-07	PC26	18 / 18 AWG 4 shielded pair / 20 AWG	150 • 46	.29 x 2.75 • 7.4 x 69.9	626 • 930
18-026-07	PC26 SP †	4 / 14 AWG 10 / 18 AWG 6 foil shielded pair / 20 AWG	150 • 46	.25 x 2.74 • 6.4 x 69.6	525 • 780
18-X26-07	PC 26	4 / 14 AWG 10 / 18 AWG 6 shielded pair / 20 AWG	150 • 46	.29 x 3.05 • 7.4 x 77.5	626 • 932



†“SP” denotes special color coding and/or conductor numbering

Use these tools to prepare Super-Flex traveling cable. See pages 90 - 91 for details.

FCJ flat cable stripper



QuickStrip wire stripper



Automatic wire stripper



Manual wire stripper



Flat Traveling Cable Type ETP/300V

SUPPORTED - UL LISTED, CSA CERTIFIED, NEC/CEC COMPLIANT

Power and signal conductors



Part Number	Product Code	Number/Size of Conductors	Steel Support Dia. inches • mm	Max. Hang Length feet • meters	Cable Nom. Dim H x W inches • mm	Cable Net Weight lbs/kft • kg/km
18-012-17	PWS 12-14	12 / 14 AWG	3/32 • 2.4	900 • 274	.24 x 2.20 • 6.1 x 56.0	444 • 659
18-020-17	PWS 20-18	20 / 18 AWG	3/32 • 2.4	900 • 274	.19 x 2.30 • 4.8 x 58.4	348 • 517
18-024-17	PWS 24-18	24 / 18 AWG	3/32 • 2.4	900 • 274	.19 x 2.69 • 4.8 x 68.3	407 • 604
18-C13-17	PWS13	4 / 14 AWG 4 shielded pair / 20 AWG 1 RG6/U coax	3/32 • 2.4	700 • 213	.38 x 2.25 • 9.5 x 57.0	590 • 876
18-C17-17	PCSX17	8 shielded pair / 20 AWG 1 RG6 coax	3/32 • 2.4	672 • 205	.38 x 2.35 • 9.5 x 60.0	616 • 915
18-C26-17	PCWS26	18 / 18 AWG 4 shielded pair / 20 AWG	3/32 • 2.4	638 • 194	.29 x 3.00 • 7.4 x 76.0	648 • 962
18-F09-17	PCWSF9	4 shielded pair / 20 AWG 1 optical fiber (62.5/125µm)	3/32 • 2.4	900 • 274	.29 x 1.50 • 7.4 x 38.0	302 • 448
18-X20-17	PCSX20	2 / 16 AWG 8 shielded pair / 20 AWG 2 RG6/U coax	3/32 • 2.4	457 • 139	.38 x 3.00 • 9.5 x 76.0	905 • 1344
18-X26-17	PCWS26	4 / 14 AWG 10 / 18 AWG 6 shielded pair / 20 AWG	3/32 • 2.4	560 • 171	.29 x 3.25 • 7.4 x 82.6	739 • 1097



Unitized construction / power and signal conductors



Part Number	Product Code	Number/Size of Conductors	Steel Support Dia. inches • mm	Max. Hang Length feet • meters	Cable Nom. Dim H x W inches • mm	Cable Net Weight lbs/kft • kg/km
18-039-17	GCWS39	6 / 14 AWG 33 / 18 AWG	3/32 • 2.4	573 • 175	.41 x 2.50 • 10.4 x 63.5	722 • 1072
18-040-17	GWS 40-18 UNITIZED	40 / 18 AWG	1/8 • 3.2	900 • 274	.39 x 2.20 • 10.0 x 56.0	646 • 959
18-K36-17	GWS 36-18 UNITIZED/ REINFORCED	36 / 18 AWG	1/8 • 3.2	900 • 274	.39 x 2.20 • 10.0 x 56.0	622 • 923

