

Deflecting sheaves/pulleys

ASSEMBLED / INCLUDES AXLE FOR KEEPER PLATES

T235 deflecting sheaves – with fixed or dismantable axles

Part Number	Sheave diameter mm	Wire rope mm	Number of grooves/ groove face width mm	Sheave width mm	Max. static load kg
G320308x	320	8.0	3 / 60	120	1580
G320408x	320	8.0	4 / 77	120	2100
G320508x	320	8.0	5 / 94	144	2600
G320608x	320	8.0	6 / 111	144	3200
G360308x	360	8.0 - 9.0	3 / 60	120	1580
G360408x	360	8.0 - 9.0	4 / 77	120	2100
G360508x	360	8.0 - 9.0	5 / 94	144	2600
G360608x	360	8.0 - 9.0	6 / 111	144	3200
G400309x	400	9.0 - 10.0	3 / 60	120	1900
G400409x	400	9.0 - 10.0	4 / 77	120	2500
G400509x	400	9.0 - 10.0	5 / 94	144	3100
G400609x	400	9.0 - 10.0	6 / 111	144	3700
G450309x	450	9.0 - 11.0	3 / 60	120	2350
G450409x	450	9.0 - 11.0	4 / 77	120	3100
G450509x	450	9.0 - 11.0	5 / 94	144	3900
G450609x	450	9.0 - 11.0	6 / 111	144	4700
G500309x	500	9.0 - 12.0	3 / 60	120	2350
G500409x	500	9.0 - 12.0	4 / 77	120	3100
G500509x	500	9.0 - 12.0	5 / 94	144	3900
G500609x	500	9.0 - 12.0	6 / 111	144	4700
G550309x	550	9.0 - 11.0	3 / 60	120	2350
G550409x	550	9.0 - 11.0	4 / 77	120	3100
G550509x	550	9.0 - 11.0	5 / 94	144	3900
G550609x	550	9.0 - 11.0	6 / 111	144	4700
G550312x	550	12.0 - 13.0	3 / 94	144	3100
G550412x	550	12.0 - 13.0	4 / 94	144	4200
G550512x	550	12.0 - 13.0	5 / 111	144	5200
G550612x	550	12.0 - 13.0	6 / 130	164	6300



For FIXED AXLES, replace the 'x' in the part number with F (i.e. G550612F)

For DISMOUNTABLE AXLES, replace the 'x' in the part number with S (i.e. G550612S)

Sizes up to 750 mm diameter are available - please call for details.