

Hydraulic Ball Valves and Pipe Fittings

BY GRINNELL

Grooved ball valves

| Part Number | Description/Size Compare to Victaulic® 726 |
|-------------|---|
| GRN-GBLV020 | Ball valve, 2 in. |
| GRN-GBLV025 | Ball valve, 2-1/2 in. |
| GRN-GBLV030 | Ball valve, 3 in. |
| GRN-GBLV040 | Ball valve, 4 in. |



Threaded ball valves*

| Part Number | Description/Size |
|-------------|--------------------------------|
| TBLV-020 | Threaded ball valve, 2 in. |
| TBLV-025 | Threaded ball valve, 2-1/2 in. |
| TBLV-030 | Threaded ball valve, 3 in. |
| TBLV-040 | Threaded ball valve, 4 in. |



*Threaded ball valves are made by Anvil.

Flexible couplings

| Part Number | Description/Size Compare to Victaulic® 77 |
|-------------|--|
| GRN-70720TS | Flexible coupling, 2 in. |
| GRN-70725TS | Flexible coupling, 2-1/2 in. |
| GRN-70730TS | Flexible coupling, 3 in. |
| GRN-70740TS | Flexible coupling, 4 in. |



Rigid couplings

| Part Number | Description/Size Compare to Victaulic® HP-70 |
|-------------|---|
| GRN-77020TS | Rigid coupling, 2 in. |
| GRN-77025TS | Rigid coupling, 2-1/2 in. |
| GRN-77030TS | Rigid coupling, 3 in. |
| GRN-77040TS | Rigid coupling, 4 in. |



Elbows and fittings

| Part Number | Description/Size Compare to Victaulic® 10 |
|-------------|--|
| GRN-21020S | 90° elbow, 2 in. |
| GRN-21025S | 90° elbow, 2-1/2 in. |
| GRN-21030S | 90° elbow, 3 in. |
| GRN-21040S | 90° elbow, 4 in. |



| Part Number | Description/Size Compare to Victaulic® 11 |
|-------------|--|
| GRN-20120S | 45° elbow, 2 in. |
| GRN-20125S | 45° elbow, 2-1/2 in. |
| GRN-20130S | 45° elbow, 3 in. |
| GRN-20140S | 45° elbow, 4 in. |



| Part Number | Description/Size Compare to Victaulic® 12 |
|-------------|--|
| GRN-31220S | 22.5° elbow, 2 in. |
| GRN-31225S | 22.5° elbow, 2-1/2 in. |
| GRN-31230S | 22.5° elbow, 3 in. |
| GRN-31240S | 22.5° elbow, 4 in. |



| Part Number | Description/Size Compare to Victaulic® 13 |
|-------------|--|
| GRN-31320S | 11.25° elbow, 2 in. |
| GRN-31325S | 11.25° elbow, 2-1/2 in. |
| GRN-31330S | 11.25° elbow, 3 in. |
| GRN-31340S | 11.25° elbow, 4 in. |



| Part Number | Description/Size Compare to Victaulic® 20 |
|-------------|--|
| GRN-21920S | Tee, 2 in. |
| GRN-21925S | Tee, 2-1/2 in. |
| GRN-21930S | Tee, 3 in. |
| GRN-21940S | Tee, 4 in. |



| Part Number | Description/Size Compare to Victaulic® 60 |
|-------------|--|
| GRN-26020S | End cap, 2 in. |
| GRN-26025S | End cap, 2-1/2 in. |
| GRN-26030S | End cap, 3 in. |
| GRN-26040S | End cap, 4 in. |



| Part Number | Description/Size |
|---------------|---------------------------|
| GRN-20NITRILS | Nitrile gasket, 2 in. |
| GRN-25NITRILS | Nitrile gasket, 2-1/2 in. |
| GRN-30NITRILS | Nitrile gasket, 3 in. |
| GRN-40NITRILS | Nitrile gasket, 4 in. |



Victaulic® is a registered trademark of the Victaulic Corporation. There is no relationship between the Victaulic Corporation and Draka Elevator. Victaulic manufactures and distributes its own products under the Victaulic® trademark.

Components
and Systems